
Touch Screen Indicator

T7-20 & S7-20



ABS and Stainless Steel Touch Screen Indicators



99 Reagent Lane • Fair Lawn, New Jersey 07410 Fax: 201-797-2287 • Toll Free Fax: 888-797-2288 • Phone: 201-797-2718 • Toll Free Phone: 800-631-0347 Email: sales@totalcomp.com • Website: www.totalcomp.com

Specifications

T7-20 & S7-20

T7-20 has ABS plastic enclosure. 6.75" touch screen display. **S7-20 has IP65 stainless steel housing**. 6.75" touch screen dislplay. 5 tactile keys for: On/Off, Set up, Home, Tare, Zero. Panel home screen keys for: Class, Take Out, Target, Count, Check, M+, Pre-Tare, Print, Sum. Applications for: Hi/Lo, Unit, Product. Built in applications include: standard weighing, over/under check weighing with bar graph, Take Out, Target, Counting, Class(grading), Hi/Lo applications. Built in Time/Date clock. Indicator has 4 Pre-Tare settings that can be saved and one Pre-Tare setting for custom entry. T7-20 and S7-20 can store up to 9999 product ID by product name, barcode, Pre-Tare, unit weight in g/pcs or Ib/pcs, Hi.Lo level. If product ID has barcode assigned to it using optional barcode scanner, product ID retrievable for fast access. M+ function will add weighment to memory that is retrievable with Sum and transferred to PC using flash drive or printed on paper and then cleared manually. USB port for plug and play ZoomSun barcode scanner and software upload and data download. T7-20 is equipped with 1xRS232 port, 1xRS422, 2x USB port. S7-20 is equipped with 1xRS232 port.

T7-20 Weight 7 lb **S7-20** Weight 8 lb

Options:

ZoomSun USB barcode scanner OS-2130D Argox direct thermal printer

Weight 2 lb Weight 2 lb





ZoomSun USB Barcode Scanner OS-2130D Argox direct thermal printer

SPECIFICATIONS	
LOAD CELL5VDC, (16)350 ohm load cells ANALOG INPUT2.5 μV/div CONVERSIONInternal count: 1,000,000 External Resolution 6000e ACCURACY0.01% of full scale OUTPUT	 KEYS

TOTALCOMP LIMITED WARRANTY

Totalcomp warrants this product to be free of defects in materials and/or workmanship and suitable for the purpose(s) intended as outlined on this sheet. This warranty is effective and shall cover the purchaser for one year from the date of shipment from our plant. If this product is found to be defective by our inspection in accordance with the above listed criteria, we will replace or repair it at our expense. For warranty service, please obtain a return authorization number from us and return the item, shipping prepaid, with a written description of the problem. We will respond promptly with the results of our evaluation.



99 Reagent Lane Fair Lawn, NJ 07410 Fax (201) 797-2287 Toll Free Fax (888) 797-2288 Phone (201) 797-2718 Toll Free Phone (800) 631-0347 Email sales@totalcomp.com Website www.totalcomp.com

TC-11/08 R.1/11